

DML's Commodity Sugars are:

COMMODITY SUGARS

BAGGED RAW SUGAR

PARAMETER	RANGE	METHOD
POLARIZATION	98,00° Z Min	Icumsa GS2/3-1 (1994)
HUMIDITY	0,200 % Max	Icumsa GS2/1/3-15 (1994)
ASHES	0,150 % Max	Icumsa GS2/3-17 (1994)
COLOR (ICUMSA)	800 - 1500 U.I. Max	Icumsa GS2/3-9 (1994)

SPECIAL WHITES

PARAMETER	RANGE	METHOD
POLARIZATION	99,70° Z Min	Icumsa GS2/3-1 (1994)
HUMIDITY	0,055 % Max	Icumsa GS2/1/3-15 (1994)
ASHES	0,050 % Max	Icumsa GS2/3-17 (1994)
COLOR (ICUMSA)	Type A: 150 U.I. Max Type B: 180 U.I. Max	Icumsa GS2/3-9 (1994)

REGULAR WHITE SUGAR (Type C)

PARAMETER	RANGE	METHOD
POLARIZATION	99,60° Z Min	Icumsa GS2/3-1 (1994)
HUMIDITY	0,065 % Max	Icumsa GS2/1/3-15 (1994)
ASHES	0,050 % Max	Icumsa GS2/3-17 (1994)
COLOR (ICUMSA)	250 U.I. Max	Icumsa GS2/3-9 (1994)

REFINED SUGAR

PARAMETER	RANGE	METHOD
POLARIZATION	99,80° Z Min	Icumsa GS2/3-1 (1994)
HUMIDITY	0,055 % Max	Icumsa GS2/1/3-15 (1994)
ASHES	0,04 % Max	Icumsa GS2/3-17 (1994)
COLOR (ICUMSA)	45 U.I. Max	Icumsa GS2/3-9 (1994)